huber

Unichiller 050

Chiller with air-cooled refrigerating unit and circulation pump (stainless steel). Housing, atmospheric open expansion tank and copper soldered evaporator made of stainless steel. With digital level indicator. For externally closed applications.

Pilot ONE:

The new Pilot ONE controller with pioneering technology and advanced control functions brings numerous advantages to routine work. The extensive features list includes a brilliant 5,7" TFT touchscreen display, USB and network connections, an integrated technical glossary and language support in 13 languages (EN, DE, FR, IT, ES, RU, CN, PT, JP, CZ, PL, KO, TR). The Pilot ONE has a convenient navigation system with easily remembered icons and menu categories which are colour sorted to make routine work simpler. Thanks to a favourites menu and One-Click operator guidance all important information is always just a few keystrokes away. Software wizards also help you to set up, ensuring correct settings. The USB port allows connection of the system to a PC or notebook. Together with the Spy software, requirements such as remote control or data transmission are easily achieved in a cost-effective manner. Network integration is easy with the internet port.

The range of functions can be expanded very easily via E-grade at any time by entering a unit specific upgrade code:

E-grade "Exclusive": TAC (True Adaptive Control) - self optimising internal and cascade control, selectable temperature control mode (Internal/Process), programmer with 3 programs (max. 15 steps), ramp function (linear), 5 point calibration, scalable graphic display, favourites menu, display resolution 0,01 K.

E-grade "Professional": Programmer with 10 programs (max. 100 steps), ramp function for temperature gradients (linear and non-linear), 2nd set point, user menus (Administrator level), calendar start.

3-2-2 warranty - registration required.

Technical data according to DIN 12876

Operating temperature range temperature set point / display Internal temperature sensor Sensor external connection Temperature stability at -10°C

Interface digital

Safety classification

Cooling power at ambient temperature +20°C

at 20°C at 0°C at -10°C at -20°C

Refrigeration machine

Refrigerant

Refrigerant quantity Circulation pump: max. delivery

max. delivery pressure Delivery at 0,3 bar Delivery at 0,5 bar Delivery at 1,0 bar Delivery at 1,5 bar Delivery at 2,0 bar Delivery at 2,5 bar Delivery at 3,0 bar

Pump connection min. filling capacity Volume of expansion

Overall dimensions WxDxH **

Net weight

sound pressure level +/- 4 dB(A)

Power supply (3 Phase) max. current (3 Phase) Fuse (3 phase) Degree of Protection -20...40 °C

5,7" colour Touchscreen

Pt100 Pt100 0,5 K

Ethernet, USB (Host u. Device), RS232 Class I / NFL

. _ .

5 kW 4,2 kW 3 kW 1,8 kW

air-cooled, CFC- and

HCFC-free R449A 1,03 kg E1 48 l/min 3,4 bar 46 l/min

3,4 bar 46 l/min 44 l/min 40 l/min 33 l/min

27 I/min 20 I/min 11 I/min G1 1/4 male

18 I 48 I

740x1165x1050 mm

283 kg 62 dB(A) 400V 3~ 50Hz * 6 A

3x10 A IP20



Order-No.: 3038.0001.01

Technical data according to DIN 12876

from Serial-No.:	313923	1.0/18
max. ambient temperature	40 °C	
min. ambient temperature	5 °C	

Technical details and dimensions are subject to change. No liability is accepted for errors or omissions. Illustrations can deviate from the original.

mini-USB cable #54949, Hose coupling for G1 1/4 male, , cover expansion tank,

Optional accessories:

Com.G@te, POKO/ECS interface, temperature control / - connection hoses, thermofluids, further accessories, etc.: see catalog.

Output data valid for: Room temperature 20°C. If the ambient temperature rises, the cooling capacity may drop.

in accordance with EN60034-1 the following voltage and frequency tolerances are valid:

Voltage + / - 5% with a simultaneous frequency tolerance of + / - 2%

Example -5% voltage and + 2% frequency -> not allowed!

-5% voltage and - 2% frequency -> allowed

Information to Electromagnetic compatibility:

Classification (disturbance) to EN55011: Class A, Group 1

Standard delivery conditions - Power cable configuration:

- 1. Single-phase devices (230V/115V) -> with cable and plug
- 2. Three-phase devices with current consumption less than 63A -> with cable, without plug
- 3. Three-phase devices with current consumption greater than 63A -> without cable, without plug

This unit is US-SNAP and applicable EU law compliant.

** Please respect space requirements. See operating conditions at www.huber-online.com

Peter Huber Kältemaschinenbau AG Werner-von-Siemens-Str. 1 D-77656 Offenburg Tel 0781/9603-0 Fax 0781/57211 www.huber-online.com